






Knappbrytare 10 AX 250 V~med rakt stående vippta 2-knappars Trapp 2knappars



Specifikation	Artikelnr.	FE	PS	EAN
 kritvit blank	2861 201 1850226	1/5	01	4010337065883
 kritvit sidenmatt	2861 27	1/5	01	4010337053286
 antracit	2861 28	1/5	11	4010337053293
 alufärg	2861 26	1/5	11	4010337053279
 rostfritt stål	2861 600	1/5	11	4010337021209

Tekniska data

Inbyggnadsdjup

- 2860 ...:	28 mm
- 2861 ...:	32 mm

Anslutningsarea

- För styva och flexibla ledare upp till:	2,5 mm ²
---	---------------------

Nominell effekt

- LEDi/ CFLi:	100 W
---------------	-------

Hänvisningar

- Beroende på tillgänglighet.