









Vippa



| Specifikation | Artikelnr. | FE | PS | EAN |
|---|---------------------|--------|----|---------------|
|  cremevit blank | 3296 01 | 10 | 21 | 4010337039341 |
|  kritvit blank | 3296 03 1850466 | 10/100 | 21 | 4010337039358 |
|  kritvit sidenmatt | 3296 27 1850467 | 10/100 | 21 | 4010337039372 |
|  antracit | 3296 28 1850469 | 10/100 | 11 | 4010337039389 |
|  alufärg | 3296 26 1850468 | 10 | 11 | 4010337039365 |
|  svart matt | 3296 005 1850464 | 10 | 11 | 4010337065593 |
|  grå matt | 3296 015 1850465 | 10 | 11 | 4010337110521 |
|  rostfritt stål | 3296 600 1850471 | 10 | 11 | 4010337043867 |