










## Montagering modularjack 2knappars Montagering MJ-01 till MJ-10



| Specifikation                                                                                         | Artikelnr.         | FE | PS | EAN           |
|-------------------------------------------------------------------------------------------------------|--------------------|----|----|---------------|
|  Montagering MJ-01  | 5601 00            | 10 | 01 | 4010337460015 |
|  Montagering MJ-02 | 5602 00<br>5140043 | 10 | 01 | 4010337460022 |
|  Montagering MJ-03 | 5603 00<br>5140045 | 10 | 01 | 4010337460039 |
|  Montagering MJ-04 | 5604 00<br>5140046 | 10 | 01 | 4010337460046 |
|  Montagering MJ-05 | 5605 00            | 10 | 01 | 4010337460053 |
|  Montagering MJ-06 | 5606 00<br>5140047 | 10 | 01 | 4010337460060 |
|  Montagering MJ-07 | 5607 00            | 10 | 01 | 4010337460077 |
|  Montagering MJ-08 | 5608 00            | 10 | 01 | 4010337460084 |
|  Montagering MJ-09 | 5609 00            | 10 | 01 | 4010337460091 |



Montagering MJ-10

5610 00

10

01

4010337460107

---

## Hänvisningar

- Endast för skruvfastsättning.
  - Lämplig för kanalinstallation.
- 

## Yttermåti mm

|                     |        |        |
|---------------------|--------|--------|
| MJ-01, MJ02, MJ-07: | B 14,8 | H 19,5 |
| MJ-03:              | B 14,8 | H 20,0 |
| MJ-04, MJ-09:       | B 14,8 | H 19,3 |
| MJ-05:              | B 16,7 | H 17,3 |
| MJ-06:              | B 15,9 | H 18,3 |
| MJ-08:              | B 14,8 | H 19,0 |
| MJ-10:              | B 16,1 | H 18,5 |

---