



Door or window contact



Specification	Order No.	Packing unit	PS	EAN
 White	0953 02	1	03	4010337953029
 brown	0953 06	1	03	4010337953067

Features

- The magnetic contact is dust- and water-protected, melted into a small glass tube (reed contact).
- Reed contact is actuated via a permanent magnet without being touched.
- Reed contact is placed in the door frame and the magnet is recessed in the door, for example.

Technical data

Contact type:	NO contact, 1-pole
Switching voltage:	max. DC 100 V
Switching current:	max. 0.5 A
Contact load capacity:	max. 10 W or 10 VA
Contact resistance:	0.15 Ω
Permissible operating voltage:	max. 40 V
Connection cable:	5 m LIYY 2 x 0.14 mm², Ø 3.2 mm

Notes

- This door or window contact is suitable for use with the alarm control unit Connect5201 00or with the I/O module5251 16.
- When making the connection to the wireless magnetic contact, use the 200 kΩ resistor enclosed with the wireless magnetic contact.
- Only block reed contacts can be used for installation in steel profiles (magnetic material).

Scope of supply

- Two surface-mounted housings, two caps, three washers 2 mm, one washer 6 mm are included in the scope of supply.

Dimensions in mm

Housing:	B 54	H 13	T 13
----------	------	------	------
