



## Light profile height 491 mm



Specification	Order No.	Packing unit	PS	EAN
 anthracite	1344 28	1	17	4010337344285
 colour aluminium	1344 26	1	17	4010337344261

Gira energy profile and light profiles with or without light elements for outdoor use. The profiles are made of powder-coated aluminium. For profiles of up to 1400 mm, the base elements are also made of powder-coated aluminium. For profiles of 1400 mm or more, the base elements are made of powder-coated steel. In each case, in the colour anthracite in accordance with the GSB standard. The surface is resistant to weather, UV, soiling, and scratching.

### Features

- The light element consists of an aluminium reflector and an impact-resistant acrylic glass plate.
- Light is also emitted from the rear as orientation light.
- A 5-pole screw terminal for rigid and flexible conductors up to 4 mm<sup>2</sup> is used for connection.

### Technical data

Protection class: IP44

### Notes

- For profile heights up to 1400 mm, an optional ground anchor can be used to facilitate mounting on a stone or concrete base.
- For profile heights of more than 1400 mm, mounting on stone or concrete is only possible using 3 heavy-duty wall anchor.
- Recommendation: Mount an RCCB prior to the device.
- Single wall plug mounting.
- Suitable for E27 light sources with energy efficiency classes A++ to E.

**Scope of supply**

- The mounting materials are included in the scope of supply.
- Light sources are not included in the scope of supply.

---

**Dimensions in mm**

Base:	B 229	H 10	T 155
Profile:	B 142	H 491	T 75

---