


Antenna socket insert (UD2410ST)



Specification	Order No.	Packing unit	PS	EAN
	0041 00	1/5	01	4010337041009

Features

- 2-gang routing box in plug-in technology.
- IEC plug for FM (radio) and DVB-T/T2.
- IEC pin jack for DVB-S/S2 (SAT).
- DC feed-through from the SAT connection to the input and bidirectional circulation between input and output with bridging of the DC voltage.
- The internal conductor is connected simply by pressing it, without the need for screws. Internal conductor can thus be removed multiple times.
- Complies with shield class A.

Technical data

TV frequency band	
- Frequency range:	5 to 862 MHz
- Decoupling:	> 25 dB
- Transmission loss:	3.5 dB
- Attenuation: R/TV plug:	8.5 dB
SAT frequency band	
- Frequency range:	950 to 2400 MHz
- Decoupling:	> 20 dB
- Transmission loss:	5 dB
- Attenuation: SAT plug:	10 dB
Installation depth:	27 mm

Notes

- For non-reflective termination of a side circuit, for use in the last antenna socket outlet.
- Suitable for terrestrial reception, area couplers, and satellite reception systems.
- For screw attachment only.