


## Surge protection module



| Specification   | Order No. | Packing unit | PS | EAN           |
|---|-----------|--------------|----|---------------|
|  | 0338 00   | 1            | 03 | 4010337128120 |

## Features

- Overvoltage module class III in accordance with IEC 61643-11 (type 3, EN 61643-11) for socket outlets with protective conductor connection.
- Mounting by snapping into place on the support ring of the socket outlet.
- With acoustic signalling to indicate faults.
- Label for indicating the socket outlet.
- Protects additional socket outlets in the circuit at a cable length of up to 5 m away.

## Technical data

|  |                   |
|--|-------------------|
| Nominal voltage $U_N$ :                        | AC 230 V~ (50 Hz) |
| Maximum continuous voltage $U_C$ :             | AC 255 V~ (50 Hz) |
| Nominal discharge surge current $I_n (8/20)$ : | 3 kA              |
| Discharge surge current $I_{total} (8/20)$ :   | 10 kA             |
| $U_{OC}$ :                                     | 6 kV              |
| max. back-up fuse:                             | 16 A              |
| $U_p$ :  | < 1.5 kV          |
| IEC/CEI 61643-11:                              | class III         |
| EN 61643-11:                                   | Type 3            |
| Protection class:                              | IP20              |
| Ambient temperature:                           | -5 °C to +40 °C   |