









SCHUKO socket outlet, 16 A 250 V~ with surgeage protection and inscription space



| Specification | Order No. | Packing unit | PS | EAN |
|---|-----------|--------------|----|---------------|
|  cream white glossy | 0451 01 | 1/5 | 02 | 4010337451013 |
|  pure white glossy | 0451 03 | 1/5 | 02 | 4010337451037 |
|  pure white matt | 0451 27 | 1/5 | 02 | 4010337451273 |
|  anthracite | 0451 28 | 1/5 | 02 | 4010337451280 |
|  colour aluminium | 0451 26 | 1/5 | 02 | 4010337451266 |
|  black matt | 0451 005 | 1/5 | 02 | 4010337037699 |
|  grey matt | 0451 015 | 1/5 | 02 | 4010337080978 |
|  red glossy | 0451 02 | 1/5 | 02 | 4010337451020 |

Features

- Protects electrical and electronic devices from transient overloads.
 - With acoustic and optical signal.
 - With screw terminals.
-

Technical data

| | |
|--|--|
| Rated voltage: | AC 230 V, 50/60 Hz |
| Rated current _{I_L} : | 16 A |
| Protection level | |
| - U _P (L/N): | ≤ 1.25 kV |
| - U _P (L/PE, N/PE): | ≤ 1.25 kV |
| Installation depth: | 31 mm |
| Ambient temperature: | -5 °C to +40 °C |
| Connection cross section | |
| - for conductors from: | 1.5 mm ² to 2.5 mm ² |

Notes

- Type 3 fine protection for electrical and electronic devices from transient overloads according to EN 61643-11.
 - Use only in combination with coarse protection type 1 and average protection type 2.
 - Use in TN, TT, and IT networks.
-

Scope of supply

- Inscription label "EDV" is enclosed.
-