



Basic Q smoke alarm device



| Specification | Order No. | Packing unit | PS | EAN |
|--|-----------|--------------|----|---------------|
|  Pure white glossy Only for countries with the official languages de, it. | 1145 02 | 1 | 03 | 4010337013525 |
|  Pure white glossy Only for countries with the official languages de, en, fr, | 1149 02 | 1 | 03 | 4010337016694 |

Increased quality criteria and technical advancements in smoke alarm devices are indicated on the market with the new Q test mark. The new Q-Label is an autonomous, manufacturer-independent quality mark for high-quality smoke alarm devices which undergo special testing for long-term use. The latest generation of Gira smoke alarm devices fulfil the criteria of the new Q-Label quality mark. The smoke alarm devices operate based on the photoelectric scattered light principle without radioactive particles. The smoke alarm devices detect smoke accumulation early and emit a warning signal before the concentration of smoke can become hazardous to people. Alerting occurs via a loud pulsing alarm tone and a flashing LED.

Features

- Only for use in private residential units or residential-like areas in accordance with DIN 14676.

Q-Label

- Tested durability and reduction of false alarms.
- Increased stability, e.g. against external factors.
- Permanently installed battery with a service life of up to 10 years.
- design According to DIN EN 14604.
- KRIWAN approval.
- Integrated function button for function test.
- Fault indication.
- Weak battery indication.

Technical data

| | |
|------------------|---------------------------------------|
| Power supply: | Via smoke alarm device battery |
| Battery life: | up to 10 years (following activation) |
| Acoustic signal: | Alarm: at least 85 dB (A) |

Illustrations are similar and may deviate from originals.

| | |
|----------------------|--------------------------|
| Optical signal: | Ring indicator (red LED) |
| Ambient temperature: | -5 °C to +55 °C |
| Installation height: | Max. 6 m |
| Protection class: | IP30 |
| Area of application: | DIN 14676 |
| Standards: | DIN 14604 |
| - design: | A |
| Batteries | |
| - Type: | 3 x CR123A |
| - UN no.: | 3091 |

Dimensions in mm

| | | |
|----------|-------|--------|
| Housing: | Ø 125 | H 38,5 |
|----------|-------|--------|
