



## Smoke alarm device Basic Q



Specification	Order No.	Packing unit	PS	EAN
 pure white glossy Only for countries with the official languages de, it.	1145 02	1	03	4010337013525
 pure white glossy Only for countries with the official languages de, en, fr,	1149 02	1	03	4010337016694

Increased quality criteria and technical advancements in smoke alarm devices are indicated on the market with the new Q test mark. The new Q-Label is an autonomous, manufacturer-independent quality mark for high-quality smoke alarm devices which undergo special testing for long-term use. The latest generation of Gira smoke alarm devices fulfil the criteria of the new Q-Label quality mark. The smoke alarm devices operate based on the photoelectric scattered light principle without radioactive particles. The smoke alarm devices detect smoke accumulation early and emit a warning signal before the concentration of smoke can become hazardous to people. Alerting occurs via a loud pulsing alarm tone and a flashing LED.

## Features

- Use in private residential units or similarly inhabited areas only in accordance with DIN 14676.

### Q-Label

- Tested durability and reduction of deceptive alarms.
- Increased stability, e.g. against external factors.
- Permanently installed battery with a service life of up to 10 years.
- Design A as per DIN EN 14604.
- KRIWAN approval.
- Integrated function button for function test.
- Fault indication.
- Weak battery indication.

## Technical data

Power supply:	Via smoke alarm device battery
Battery life:	up to 10 years (after activation)
Acoustic signal:	Alarm: at least 85 dB (A)

Illustrations are similar and may deviate from originals.

Visual signal:	Ring indicator (red LED)
Ambient temperature:	-5 °C to +55 °C
Installation height:	max. 6 m
Protection type:	IP42
Area of application:	DIN 14676
Standards:	DIN 14604
- Design:	D
Batteries	
- Type:	3 x CR123A
- UN no.:	3091

---

## Dimensions in mm

Housing:	Ø 125	H 38,5
----------	-------	--------

---