


LED orientation light 230 V~ RGB



| Specification | Order No. | Packing unit | PS | EAN |
|---|-----------|--------------|----|---------------|
|  | 1169 00 | 1 | 02 | 4010337042341 |

Features

- LED orientation light for private and commercial use.
- The orientation light is used, for example, to illuminate stairs or as an orientation aid in dark rooms.
- RGB LEDs are used as light sources.
- The light colours white, blue, red, green and orange can be set consecutively, or a continuous colour cycle over the entire range of colours (approx. 5 min.) can be started via a control input.
- As a result, any desired colour can be set by stopping at the corresponding point.
- The brightness of the light can be set individually.
- A film which can be inscribed individually can be laid in the cover plate.
- Pictograms for room and route marking can be inserted.

Technical data

| | |
|--------------------------|---------------------|
| Rated voltage: | AC 230 V, 50 Hz |
| Power consumption: | 1.8 W/2.0 VA |
| Light intensity (white): | 1.2 cd |
| Installation depth: | 30 mm |
| Connections | |
| - maximum: | 1.5 mm ² |
| Ambient temperature: | -15 °C to +40 °C |

Notes

- Professional labelling with the Gira Inscription Service www.marking.gira.com.

Scope of supply

- A stainless-steel slat (for glare reduction) is included with the LED orientation light.
