


External camera



Specification	Order No.	Packing unit	PS	EAN
 pure white	1220 00	1	10	4010337100058

Features

- External camera for wall or ceiling mounting with variable lens, integrated IR LED illumination, and automatic white balance.
- The camera can be installed anywhere in the entrance area and integrated in the Gira door communication system via the DCS-camera gateway.
- Light-sensitive chip set for clear imaging in weak light conditions.
- Adjustable IR LEDs for video monitoring in complete darkness.
- Easy-plug camera module and mounting plate for easy, rapid installation.
- Second video output for connecting a monitor during commissioning.
- Camera module adjustable on three axes.

Technical data

Rated voltage:	DC 12 V +10 %
Rated voltage:	AC 24 V +10 %
Current consumption	
- DC 12 V:	max. 450 mA
- AC 24 V:	max. 5 mA
Connections:	1 x video (HD TVI, BNC), 1 x video (FBAS, BNC), 1 x power supply (DC)
Camera	
- Image sensor:	1/3" CMOS progressive scan
- Type:	Vario Dome
- Lens:	2.8 to 12 mm; varifocal lens
- Resolution:	720p25, 720p30
- Horizontal angle of vision:	28° to 78°
Day/night switching:	Electromechanical IR cut filter
Electronic shutter control:	1/25 to 1/50 000 s
Camera control:	On-screen display (OSD)
Background lighting compensation:	DWDR

Digital zoom:	Yes
Video system:	HD TVI
Minimal lighting	
- Day:	0.1 lux
- B/W:	0.001 lx
- IR mode:	0 lx (F2.0)
IR LED:	24 LEDs
IR range:	20 m
Ambient temperature:	-20°C to +60°C
Protection type:	IP66
Humidity:	max. 90%
Weight:	approx. 950 g

Dimensions in mm

External camera:	Ø 143	H 125
------------------	-------	-------
