


Surface-mounted home station



Specification	Order No.	Packing unit	PS	EAN
 <p>pure white glossy</p>	1250 112	1	18	4010337047391

Features

- Fully pre-assembled surface-mounted home station. This facilitates fast and clean installation.
- Integrating the design variants of the various design lines creates a uniform appearance of the door communication system and electrical installation.
- Installation possible with or without frame.
- Easy mounting using plug-in screw terminals on the mounting plate. Contact to the home station is established when the home station is attached to the mounting plate.
- Simple disassembly of the home station during renovation work.
- Mounting holes for installation.
- Signal transmission and power supply of home station via reverse-polarity-protected and short-circuit-proof 2-wire bus.
- Parallel connection of up to three home stations is possible (with power supply via the 2-wire bus).
- One-man commissioning with simple commissioning procedure.
- Ringing tone differentiation for door call, internal call and floor call.
- Selection of five different ringing tone melodies which can be individually assigned to specific call buttons.
- Hands-free feature (voice-controlled talk-back with echo and background noise suppression).
- Enforcement function in the event of loud background noise during voice connection.
- Eavesdropping prevention.
- Operating buttons with integrated LEDs for status display.

The operating buttons of the surface-mounted home station control the following functions in connection with the switching actuator or the flush-mounted switching actuator:

- Switching of lights and other functions.
- Controlling the door opener.
- Setting the ringing tone melody.
- Switching the ringing tone on and off.
- Accepting calls.
- Activation of the enforcement function.
- Adjustment of ring tone and voice volume.

Technical data

Power supply: DC 26 V \pm 2 V (by 2-wire bus)

Ambient temperature: 0 °C to +50 °C

Connections

- 2-wire bus: 2 x screw terminal

Illustrations are similar and may deviate from originals.

- Floor-call button: 2 x screw terminal

Dimensions

- System 55: B 55 x H 127 x T 20 mm
- Gira F100: B 70 x H 142 x T 20 mm

Notes

- Installation without frame is possible.
 - A 2-gang cover frame without crossbar is required for installation with System 55 or Gira F100.
 - A frame is required for installation in a device box
 - This component enables door communication systems with up to 70 devices to be set up (e.g. 1 x built-in speaker, 5 x add-on modules for built-in speakers, 68 x surface-mounted home stations).
-