




## Surface-mounted door station video, 3 gang



| Specification  | Order No. | Packing unit | PS | EAN           |
|--|-----------|--------------|----|---------------|
|  pure white         | 1270 66   | 1            | 10 | 4010337270669 |
|  anthracite       | 1270 67   | 1            | 10 | 4010337270676 |
|  colour aluminium | 1270 65   | 1            | 10 | 4010337270652 |

## Features

- Fully pre-assembled surface-mounted door station for vertical surface-mounted installation. This facilitates fast and clean installation.
- In the design of the Gira TX\_44 design line.
- Torsion-resistant surface-mounted housing due to aluminium profile.
- Frame made of shatter-proof thermoplastic with high resistance to ultraviolet light as well as a scratch-resistant, care-free surface.
- Theft protection ensured by screws with hexalobular socket.
- Signal transmission and supply of the audio and video components via reverse-polarity-protected and short-circuit-proof 2-wire bus.
- One-man commissioning with simple commissioning procedure.
- Weather-resistant loudspeaker.
- High-quality electret microphone.
- Hands-free feature (voice-controlled talk-back with echo and background noise suppression).
- Acknowledgement tone when call button is pressed.
- Voice volume adjustable.
- White call-button illumination with LED technology. Even, clearly visible call button illumination is achieved via maintenance-free, energy-saving LED technology.
- Sprayed-water proof call-button cover plate made of shock-resistant plastic.
- Name plate of the call button can be exchanged without tools and frame removal.
- Professional inscription by the Gira inscription service [www.beschriftung.gira.de](http://www.beschriftung.gira.de) or the Gira inscription software.
- Automatic day or night switching: the camera switches from day mode (colour display) to night mode (black and white display) and back again at a defined ambient brightness. Due to the high degree of light sensitivity in night mode, good presentation results are achieved even in poor lighting conditions.
- LEDs ensure steady illumination of the field of view at close proximity in night mode.
- Camera can be manually pivoted 20° horizontally and vertically. In combination with the wide-angle lens, a very wide field of view results.
- Automatic background lighting compensation.

- Automatic white balance.
- Automatic gain control (AGC).
- Integrated camera heating with temperature detection.
- Sprayed-water proof cover plate.
- Camera cover plate made of impact-resistant plastic. Easy to replace if damaged, e.g. due to vandalism.

---

## Technical data

|   |                                   |
|---|-----------------------------------|
| Power supply:                                     | DC 26 V $\pm$ 2 V (by 2-wire bus) |
| Connections                                       |                                   |
| - 2-wire bus:                                     | 2 x screw terminal                |
| - Additional power supply:                        | 2 x screw terminal                |
| Protection class:                                 | IP44                              |
| Ambient temperature:                              | -25 °C to +70 °C                  |
| Image capture element:                            | CCD sensor 0.85 cm (1/3")         |
| Wide-angle lens:                                  | 150°                              |
| Visible range of detection:                       | 100°                              |
| Detection range (when pivoted by 20°):            | 140°                              |
| Colour system:                                    | PAL                               |
| Pixels:   | 500 (H) x 582 (V)                 |
| Horizontal resolution:                            | 380 TV lines                      |
| Switchover threshold for colour to B/W operation: | 1 lx                              |
| Light sensitivity in B/W operation:               | 0.1 lx                            |
| Electronic shutter speed::                        | up to 1/100000 s                  |
| IR filter:  | integrated                        |
| Recommended installation height for camera:       | 1.50 m                            |

---

## Notes

- Call buttons which are not required can be covered with the call-button cover plate for call button, 3-gang.

---

## Dimensions in mm

|                 |       |       |      |
|-----------------|-------|-------|------|
| without camera: | B 110 | H 253 | T 19 |
| with camera:    | B 110 | H 253 | T 40 |
| Name plates:    | B 62  | H 18  | T -  |