

**Gira energy profile with 6 empty units height 769 mm  
not equipped**



| Specification  | Order No. | Packing unit | PS | EAN           |
|--|-----------|--------------|----|---------------|
|  anthracite        | 1351 28   | 1            | 17 | 4010337351283 |
|  colour aluminium | 1351 26   | 1            | 17 | 4010337351269 |

Gira energy profile and light profiles with or without light elements for outdoor use. The profiles are made of powder-coated aluminium. For profiles of up to 1400 mm, the base elements are also made of powder-coated aluminium. For profiles of 1400 mm or more, the base elements are made of powder-coated steel. In each case, in the colour anthracite in accordance with the GSB standard. The surface is resistant to weather, UV, soiling, and scratching.

## Features

- Freely configurable Gira energy profile with 6 empty units.
- The six empty units can be individually equipped with device inserts from the Gira TX\_44 design line or from System 55 by the customer.

## Technical data

Protection type (device cover closed): IP44

### Dimensions

- Base: W 229 x H 10 x D 155 mm  
- Profile: W 142 x H 769 x D 75 mm

## Notes

- For profile heights up to 1400 mm, an optional ground anchor can be used to facilitate mounting on a stone or concrete base.
- For profile heights of more than 1400 mm, mounting on stone or concrete is only possible using 3 heavy-duty wall anchor.
- Recommendation: Mount an RCCB prior to the device.
- Single wall plug mounting.

## Scope of supply

- Two cover frames Gira TX\_44, 3-gang are included with delivery.
- The mounting materials are included with delivery.

---