



**Gira Energy profile with light element and 3 empty units, height 1600 mm
Not outfitted**



Specification	Order No.	Packing unit	PS	EAN
 anthracite	1353 28	1	17	4010337353287
 colour aluminium	1353 26	1	17	4010337353263

Gira energy profile and light profiles with or without light elements for outdoor use. The profiles are made of powder-coated aluminium. For profiles of up to 1400 mm, the base elements are also made of powder-coated aluminium. For profiles of 1400 mm or more, the base elements are made of powder-coated steel. In each case, in the colour anthracite in accordance with the GSB standard. The surface is resistant to weather, UV, soiling, and scratching.

Features

- Freely configurable Gira energy profile with 3 empty units and light element.
- The light element consists of an aluminium reflector and an impact-resistant acrylic glass plate.
- Light is also emitted from the rear as orientation light.
- The three empty units can be individually outfitted with device inserts from the TX_44 or System 55 ranges by customers.

Technical data

Protection type (device cover closed): IP44

Notes

- For profile heights up to 1400 mm, an optional ground anchor can be used to facilitate mounting on a stone or concrete base.
- For profile heights of more than 1400 mm, mounting on stone or concrete is only possible using 3 heavy-duty wall anchor.
- Recommendation: Mount an RCCB prior to the device.
- Mounting with three heavy-duty dowels.
- Light sources with E27 treading of the energy efficiency classes A++ to E can be used.
- Any required electrical isolation of mains and low voltage can be implemented with the included accessories.

Scope of supply

- A 3-gang TX_44 frame is included in the scope of supply.
- The mounting materials are included in the scope of supply.
- Light sources are not included in the scope of supply.

Dimensions in mm

Base:	W 229	H 10	D 155
Profile:	W 142	H 1600	D 75
