



## Gira energy profile with 4 empty units height 1600 mm not equipped



Specification	Order No.	Packing unit	PS	EAN
 anthracite	1356 28	1	17	4010337356288
 colour aluminium	1356 26	1	17	4010337356264

Gira energy profile and light profiles with or without light elements for outdoor use. The profiles are made of powder-coated aluminium. For profiles of up to 1400 mm, the base elements are also made of powder-coated aluminium. For profiles of 1400 mm or more, the base elements are made of powder-coated steel. In each case, in the colour anthracite in accordance with the GSB standard. The surface is resistant to weather, UV, soiling, and scratching.

### Features

- Freely configurable Gira energy profile with 4 empty units.
- The four empty units can be individually equipped with device inserts from the Gira TX\_44 design line or from System 55 by the customer.

### Technical data

Protection type (device cover closed): IP44

### Notes

- For profile heights up to 1400 mm, an optional ground anchor can be used to facilitate mounting on a stone or concrete base.
- For profile heights of more than 1400 mm, mounting on stone or concrete is only possible using 3 heavy-duty wall anchor.
- Recommendation: Mount an RCCB prior to the device.
- Mounting using three heavy-duty wall anchors.
- Any required electrical isolation of mains and low voltage can be implemented with the included accessories.

## Scope of supply

- Gira TX\_44 cover frame, 4-gang included with delivery.
  - The mounting materials are included with delivery.
- 

## Dimensions in mm

Base:	B 229	H 10	T 155
Profile:	B 142	H 1600	T 75

---