

Continuous controller with button interface, 4-gang for KNX



Specification	Order No.	Packing unit	PS	EAN
cream white glossy	2100 01	1	06	4010337048022
pure white glossy	2100 03	1	06	4010337048039
pure white matt	2100 27	1	06	4010337048060
anthracite	2100 28	1	06	4010337048077
colour aluminium	2100 26	1	06	4010337048053
black matt	2100 005	1	06	4010337037255
grey matt	2100 015	1	06	4010337083016
stainless steel	2100 600	1	06	4010337021520

Features

- The setpoint value is changed using the adjustment dial.
- A presence button is used to switch between Comfort and Standby mode.
- The current statuses are displayed on the continuous controller by LEDs.
- This control has the following control functions: TE(1,2,3,0,0,0,0,0)

Technical data

Installation depth: 23 mm

Connection cross section
- J-Y(St)Y: 2 × 2 × 0.8 mm²
