


## KNX IP router



Specification	Order No.	Packing unit	PS	EAN
 DRA plus	2167 00	1	26	4010337084440

## Features

- Connection of KNX lines with aid of data networks and use of the Internet protocol (IP).
- Coupling of a KNX system together with the Gira HomeServer or Gira FacilityServer.
- Filtering and forwarding of telegrams.
- Use as line or area coupler.
- Use as KNX clock.
- Recording of KNX telegrams on a microSD card.
- Hardware from index status I14 prepared for KNX Secure (additional firmware update required).
- Up to four tunnelling connection possible simultaneously.
- Reliable communication for automatic correction of telegram losses in WLAN (Reliable Communication).

## Technical data

KNX medium:	KNXnet/IP and TP1-256
Rated voltage:	DC 24 to 30 V
IP communication:	Ethernet 10/100 BaseT (10/100 Mbit/s)
Supported protocols:	ARP, ICMP, IGMP, DHCP, AutoIP, UDP/IP (Core, Routing, Tunneling, Device Management)
microSD card:	up to 32 GB
Connections	
- IP:	RJ45 jack
- KNX:	Connection and junction terminal
Ambient temperature:	0 °C to +45 °C

## Notes

- Supply via external DC 24 V.
  - The Gira Project Assistant (GPA) is required for firmware updates. The GPA is available free of charge in the Gira download area.
- 

## Scope of supply

- microSD card is not included in the scope of supply.
- 

## Dimensions

Modular widths (MW): 2

---