


## System 2000 automatic control switch 2 Komfort top unit, mounting height up to 2.20 m



Specification	Order No.	Packing unit	PS	EAN
 Aluminium (lacquered)	2302 203	1/5	02	4010337106500

Automatic control switch for switching light automatically, depending on the movement of heat and ambient brightness.

### Features

- Extension of the detection range in combination with an auxiliary insert for presence detectors and automatic control switches.
- Teach-in function for adapting the brightness threshold.
- Switch-on brightness can be saved permanently, with dimming insert.
- Can be dimmed slightly, with dimming insert and connected auxiliary insert.
- Crawl-under protection.
- Delay time limit.
- IR remote control for setting various functions.
- Dimming function, with dimming insert.
- Short-term operation, e.g. for controlling acoustic signal transmitters, with switching insert.
- Display LED.
- Occupied-home simulation.
- Nightlight function.
- Motion detection which can be toggled between the indoors and outdoors.

### Technical data

Mounting height:	1.10 m / 2.20 m
Mounting height of 2.20 m	
- Range of detection forwards::	approx. 12 m
- Range to each side:	approx. 6 m
Mounting height up to 1.10 m	
- Range of detection forwards::	approx. 6 m
- Range to each side:	approx. 3.6 m
Detection angle:	180°
Brightness value	
- adjustable:	approx. 1 to 200 lx

Illustrations are similar and may deviate from originals.

- fixed:	Day mode
Locking time:	approx. 0.3 to 4 s
Protection type	
- System 55, Gira E22, Gira F100:	IP20
- TX_44:	IP44
Ambient temperature:	-15 °C to +45 °C
Sensitivity:	100 to 25 %
Delay time:	approx. 10 s to 60 min
Short-term operation	
- Pulse duration:	approx. 0.3 second
- Pulse pause:	approx. 2.7 second
Battery	
- Type:	
Battery:	

---

## Notes

- For operation with System 2000 flush-mounted insert for dimming, switching, or auxiliary insert use for presence detectors and automatic control switches.

---

## Scope of supply

- IR remote control.

---