



System 3000 LED rotary dimming insert Basic RC



| Specification | Order No. | Packing unit | PS | EAN |
|---|-----------|--------------|----|---------------|
|  | 2457 00 | 1 | 02 | 4010337131458 |

Features

- Device operates on trailing edge principle.
- It is switched on with a bulb-saving soft start.
- Push-button/2-way switch for integration in 2-way switching and intermediate switching configurations.
- Minimum brightness can be adjusted.
- Maximum brightness can be adjusted.
- Electronic short-circuit and overload protection.
- Electronic excess-temperature protection.
- No neutral conductor required.

Technical data

| | |
|---|--|
| Rated voltage: | AC 230 V, 50/60 Hz |
| Standby: | None |
| Connected load at 35°C: | |
| - HV LED lamps (trailing edge): | Typically 3 to 200 W |
| - Light bulbs: | 3 to 200 W |
| - HV halogen lamps: | 3 to 200 W |
| - Electronic transformer with LV LED (trailing edge): | Typically 3 to 200 W |
| Cable length | |
| - Load: | Max. 100 m |
| Installation depth: | 24 mm |
| Installation: | in device box in accordance with DIN 49073 |
| Ambient temperature: | 0°C to +35°C |