








## Bluetooth® wall transmitter, 1-gang



| Specification   | Order No. | Packing unit | PS | EAN           |
|---|-----------|--------------|----|---------------|
|  cream white glossy  | 2461 01   | 1            | 02 | 4010337110712 |
|  pure white glossy | 2461 03   | 1            | 02 | 4010337101598 |
|  pure white matt   | 2461 27   | 1            | 02 | 4010337101604 |
|  anthracite        | 2461 28   | 1            | 02 | 4010337101611 |
|  colour aluminium  | 2461 26   | 1            | 02 | 4010337101628 |
|  black matt        | 2461 005  | 1            | 02 | 4010337101635 |
|  grey matt         | 2461 015  | 1            | 02 | 4010337110729 |

### Features

- Wireless transmitter for transmitting switching, dimming or blind commands to the Bluetooth® wireless receivers from the System 3000 or third parties, e.g Casambi.
- Battery-free device without external power supply. The transmission energy is generated from mechanical energy by actuating the rocker.

- Configuration via the app or NFC.

---

## Technical data

|                      |                                  |
|----------------------|----------------------------------|
| Wireless frequency:  | 2.402 - 2.480 GHz                |
| Wireless protocol:   | Bluetooth® low energy (BLE)      |
| Interface:           | NFC                              |
| Range                |                                  |
| - in free field:     | up to 75 m                       |
| - in buildings:      | approx. 10 m                     |
| Ambient temperature: | -25 °C to +65 °C                 |
| Humidity:            | 0 to 95 % (without condensation) |

---

## Notes

- Mounting on device box or on smooth, level surfaces using screws or adhesives.
  - This product cannot be used with eNet.
- 

## Scope of supply

- Radio wall transmitter, comes with mounting plate, adhesive film (privacy protection for glass surfaces), and adhesive points for installation on smooth, level surfaces.
-