



## System 3000 motion detector top unit 2.20 m Standard Gira F100



Specification	Order No.	Packing unit	PS	EAN
 pure white glossy	5375 112	1/5	02	4010337051213

### Features

- Automatic switching of lighting, depending on the movement of heat and ambient brightness.
- Operation with System 3000 switching or dimming insert or 3-wire auxiliary insert.
- Expansion of the detection range in combination with the 3-wire auxiliary insert.
- Adjustable brightness threshold.
- Sensitivity adjustable in four steps.
- If a System 3000 auxiliary insert with operating top unit or mechanical button is connected to the main unit, the lighting can be switched on or dimmed for the duration of the delay time.

With System 3000 dimming insert

- Switch on with the last brightness set, or a saved switch-on brightness.
- The switch-on brightness can only be saved permanently via the System 3000 auxiliary insert with operating top unit.

### Technical data

Angle of detection:	180°
Brightness value	
- adjustable:	approx. 5 to 500 lx
- fixed:	Day mode
Sensitivity:	25, 50, 75, 100 %
Protection class	
- System 55, Gira F100:	IP20
- TX_44:	IP44
Delay time:	approx. 2 min fixed
Mounting height up to 2.20 m	
- Range of detection forwards:	Max. 15 m
- Range to each side:	Max. 10 m
Mounting height up to 1.10 m	
- Range of detection forwards:	Max. 10 m

Illustrations are similar and may deviate from originals.

- Range to each side:

Max. 9 m

Ambient temperature:

-20 °C to +45 °C

---