

eNet wireless control unit 1 – 10 V, 1-gang Mini



Specification	Order No.	Packing unit	PS	EAN
	5421 00	1/5	42	4010337774174

Features

- The eNet wireless control unit enables the switching and brightness setting of lights with 1 - 10 V interface.
- Switch-on and minimum brightness can be saved.
- Scene operation.
- Status display of the 1 - 10 V devices via LED.
- Status feedback to eNet wireless transmitter.

Can be set with eNet server:

- Maximum brightness.
- Dimming speed.
- Delay time.
- Switch-on/off delay.
- Dimming ramp up/down.
- Switch-off pre-warning.
- Permanent-on, permanent-off.
- Hotel function.
- Light control.
- Repeater function.
- Localisation of the device.

Technical data

Rated voltage:	AC 230 V, 50/60 Hz
Standby:	max. 0.5 W
Ambient temperature:	-25 °C to +70 °C
Control current:	max. 50 mA
Switching current	
- Ohmic load:	6 A
- Fluorescent lamps:	3 AX
Connected load	
- Ohmic load:	1380 W

Illustrations are similar and may deviate from originals.

- Capacitive load:	690 VA (560 µF)
Connections:	max. 4 mm ²
Wireless frequency:	868.0 to 868.6 MHz
Range (free field):	approx. 100 m

Notes

- Installation in device box, surface-mounted housing, or in an installation adapter.
 - Wireless approval is valid for EU and EFTA countries.
-

Dimensions in mm

Ø 53 H 28
