


## eNet wireless control unit DALI, 1-gang Mini



| Specification   | Order No. | Packing unit | PS | EAN           |
|---|-----------|--------------|----|---------------|
|  | 5422 00   | 1/5          | 42 | 4010337774198 |

### Features

- The eNet wireless control unit DALI enables switching and brightness adjustment of DALI lights.
- Joint operation of all connected DALI ballasts, broadcast.
- DALI power supply for a maximum of twelve devices.
- Parallel connection of up to six DALI wireless control units Mini to supply power to up to 72 devices.
- Switch-on and minimum brightness can be saved.
- Scene operation.
- Status feedback to eNet radio transmitter.
- Short-circuit and excess-temperature protection.

Can be set with eNet server:

- Maximum brightness.
- Dimming speed.
- Delay time.
- Switch-on/off delay.
- Dimming ramp up/down.
- Switch-off pre-warning.
- Permanent-on, permanent-off.
- Hotel function.
- Light control.
- Repeater function.
- Localisation of the device.

### Technical data

|                           |                        |
|---------------------------|------------------------|
| Rated voltage:            | AC 230 V, 50/60 Hz     |
| Standby:                  | max. 2 W               |
| Ambient temperature:      | -25 °C to +70 °C       |
| DALI rated voltage:       | DC 16 V                |
| Output current:           | max. 24 mA             |
| Connection cross section: | Max. 4 mm <sup>2</sup> |

Illustrations are similar and may deviate from originals.

Wireless frequency: 868.0 to 868.6 MHz

Range (free field): approx. 100 m

---

## Notes

- Mounting in device box, surface-mounted housing or in installation adapter.
  - Radio approval is valid for EU and EFTA countries.
- 

## Dimensions in mm

Ø 53      H 28

---