


## eNet wireless DALI control unit, 1-gang Mini



Specification	Order No.	Packing unit	PS	EAN
	5422 00	1/5	42	4010337774198

### Features

- The eNet wireless DALI control unit enables the switching and brightness setting of DALI lights.
- Joint operation of all connected DALI control equipment, broadcast.
- DALI supply for a maximum of twelve devices.
- Parallel switching of up to six DALI wireless control units Mini to supply power to up to 72 devices.
- Switch-on and minimum brightness can be saved.
- Scene operation.
- Status feedback to eNet wireless transmitter.
- Short-circuit and excess-temperature protection.

Can be set with eNet server:

- Maximum brightness.
- Dimming speed.
- Delay time.
- Switch-on/off delay.
- Dimming ramp up/down.
- Switch-off pre-warning.
- Permanent-on, permanent-off.
- Hotel function.
- Light control.
- Repeater function.
- Localisation of the device.

### Technical data

Rated voltage:	AC 230 V, 50/60 Hz
Standby:	max. 2 W
Ambient temperature:	-25 °C to +70 °C
DALI rated voltage:	DC 16 V
Output current:	max. 24 mA
Connections:	max. 4 mm <sup>2</sup>

Illustrations are similar and may deviate from originals.

Wireless frequency: 868.0 to 868.6 MHz

Range (free field): approx. 100 m

---

## Notes

- Installation in device box, surface-mounted housing, or in an installation adapter.
  - Wireless approval is valid for EU and EFTA countries.
- 

## Dimensions in mm

Ø 53      H 28

---