

## eNet wireless switching/momentary-contact actuator 1-gang Mini



Specification	Order No.	Packing unit	PS	EAN
	5423 00	1/5	42	4010337774204

### Features

- The eNet wireless switching of momentary-contact actuator enables switching of lighting.
- Operating modes: Switching actuator or momentary-contact actuator.
- Status feedback to eNet wireless transmitter.
- Scene operation.
- Operating mode buttons: Relay contact stays closed as long as telegrams are being received (max. 60 seconds).

Can be set with eNet server:

- Flashing function.
- Delay time.
- Switch-on/off delay.
- Switch-off pre-warning.
- Minimum switching repeat time.
- Permanent-on, permanent-off.
- Repeater function.
- Localisation of the device.

### Technical data

Rated voltage:	AC 230 V, 50/60 Hz
Standby:	max. 0.5 W
Ambient temperature:	-25 °C to +70 °C
Switching capacity AC 230 V:	16 A / AC1
Connected load	
- Light bulbs:	2300 W
- HV halogen lamps:	2000 W
- Wound transformer:	1000 VA
- Tronic transformer:	1500 W
- Fluorescent lamps, uncompensated:	920 VA
- LED lamps:	typ. 500 W

- Compact fluorescent lamp:	typ. 500 W
- Capacitive load:	690 VA (560 µF)
Connections:	max. 4 mm <sup>2</sup>
Wireless frequency:	868.0 to 868.6 MHz
Range (free field):	approx. 100 m

---

## Notes

- Installation in device box, surface-mounted housing, or in an installation adapter.
  - Wireless approval is valid for EU and EFTA countries.
- 

## Dimensions in mm

Ø 53      H 28

---