


eNet Radio blind actuator, 1-gang Mini



Specification	Order No.	Packing unit	PS	EAN
	5427 00	1/5	42	4010337774235

Features

- The eNet wireless blind actuator enables the control of electrically operated hangings such as blinds, shutters and awnings.
- Positioning of blinds and slats using scene call-up.
- Positions for sun protection and twilight can be saved.
- Status feedback to eNet radio transmitter.
- Hanging travel time can be saved.
- Slat adjustment time can be saved.

Can be set with eNet server:

- Adjustment time when changing directions.
- Direction of travel can be inverted (e.g. for roof windows).
- Position for solar protection, twilight, lock-out protection, and wind alarms.
- Behaviour after mains power failure.
- Repeater function.
- Localisation of the device.

Technical data

Rated voltage:	AC 230 V, 50/60 Hz
Standby:	max. 0.5 W
Ambient temperature:	-25 °C to +70 °C
Connected load of motors:	1000 W
Connection cross section:	Max. 4 mm ²
Wireless frequency:	868.0 to 868.6 MHz
Range (free field):	approx. 100 m

Notes

- Mounting in device box, surface-mounted housing or in installation adapter.
 - Radio approval is valid for EU and EFTA countries.
-

Dimensions in mm

Ø 53 H 28
