

## eNet wireless blind actuator, 1-gang



| Specification | Order No. | Packing unit | PS | EAN              |
|---------------|-----------|--------------|----|------------------|
|               | DRA       | 5437 00      | 1  | 42 4010337774297 |

### Features

- The eNet wireless blind actuator receives telegrams for controlling electrically operated hangings such as blinds, shutters and awnings from the eNet wireless receiver module or eNet server via a data line.
- Positioning of blinds and slats using scene call-up.
- Positions for sun protection and twilight can be saved.
- Threshold value scenes for solar protection, twilight and wind alarms.
- Status feedback to eNet radio transmitter.
- Curtain runtime can be saved.
- Slat adjustment time can be saved.

Can be set with eNet server:

- Adjustment time when changing directions.
- Direction of travel can be inverted (e.g. for roof windows).
- Position for solar protection, twilight, lock-out protection, and wind alarms.

### Technical data

|                           |                        |
|---------------------------|------------------------|
| Rated voltage:            | AC 230 V, 50/60 Hz     |
| Standby:                  | max. 0.2 W             |
| Ambient temperature:      | -5 °C to +45 °C        |
| Connected load of motors: | 1000 W                 |
| Connection cross section: | Max. 4 mm <sup>2</sup> |

### Notes

- An eNet wireless receiver module or an eNet server is required to operate this DIN rail adapter.
- Radio approval is valid for EU and EFTA countries.

## Dimensions

Modular width (MW): 2

---