


## eNet wireless energy sensor, 1-gang Mini



Specification	Order No.	Packing unit	PS	EAN
	5471 00	1/5	42	4010337774365

### Features

- The eNet wireless energy sensors enable the wireless transmission of voltage, electricity, and energy values to the eNet server.
- Logging electricity and voltage of the connected device.
- Calculation of effective output, reactive power, apparent power, and active electrical energy.
- Event-controlled or time-controlled transmission of measurement value telegrams to the eNet server.
- Time synchronisation with the eNet server.

### Technical data

Rated voltage:	AC 230 V, 50/60 Hz
Ambient temperature:	-5 °C to +45 °C
Measurement range	
- Electricity:	0 mA to 16 A
- Electrical power:	0 to 3680 W
- Energy consumption:	0 to 99999 kWh
Wireless frequency:	868.3 MHz
Range (free field):	approx. 100 m
Rated load current:	16 A
Connections:	max. 4 mm <sup>2</sup>

### Notes

- Installation in device box, surface-mounted housing, or in an installation adapter.
- Wireless approval is valid for EU and EFTA countries.

# GIRA Data sheet

[catalogue.gira.com](http://catalogue.gira.com)

© Copyright by  
Gira Giersiepen GmbH & Co. KG  
All rights reserved

[www.gira.com](http://www.gira.com)

## Dimensions in mm

Ø 53

H 23

---