


## Surge protection module



| Specification  | Order No. | Packing unit | £/piece<br>without VAT | PS | EAN           |
|--|-----------|--------------|------------------------|----|---------------|
|  | 0338 00   | 1            | 76.31                  | 03 | 4010337128120 |

## Features

- Overvoltage module class III in accordance with IEC 61643-11(type 3, EN 61643-11) for socket outlets with protective conductor connection.
- Mounting by snapping into place on the support ring of the socket outlet.
- With acoustic signalling to indicate faults.
- Label for indicating the socket outlet.
- Protects additional socket outlets in the circuit at a cable length of up to 5 m away.

## Technical data

|   |                   |
|---|-------------------|
| Nominal voltage $U_N$ :                       | AC 230 V~ (50 Hz) |
| Maximum continuous voltage $U_C$ :            | AC 255 V~ (50 Hz) |
| Nominal discharge surge current $I_n$ (8/20): | 3 kA              |
| Discharge surge current $I_{total}$ (8/20):   | 10 kA             |
| $U_{oc}$ :                                    | 6 kV              |
| max. back-up fuse:                            | 16 A              |
| $U_p$ :                                       | < 1.5 kV          |
| IEC/CEI 61643-11:                             | class III         |
| EN 61643-11:                                  | Type 3            |
| Protection class:                             | IP20              |
| Ambient temperature:                          | -5 °C to +40 °C   |