


Staircase light timer



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 DRA	0821 00	1	101.09	02	4010337821007

Features

- Manual or automatic light switching in staircases.
- Switch light on using System 2000 and System 3000 impulse insert or rocker buttons.
- Delay time adjustable.
- Electronic overload protection for the control input.
- Automatic function with or without a switch-off pre-warning.
- Switch light on or off permanently.
- Insert in 3 or 4-conductor circuit.

Technical data

Rated voltage:	AC 230 V, 50 Hz
Current load of control input A1:	40 mA
Switching voltage:	AC 250 V
Ohmic switching current:	16 A
Switch-on current 20 ms:	max. 165 A
Minimum switching current AC:	100 mA
Connected load	
- HV LED lamps:	typically 400 W
- Light bulbs:	2300 W
- HV halogen lamps:	2300 W
- Tronic transformer:	1500 W
- Wound electronic transformer:	1000 VA
- Fluorescent lamps, uncompensated:	1200 VA
- Fluorescent lamps, lead-lag circuit:	2300 (140 µF)
- Fluorescent lamps, parallel-compensated:	920 VA
- Electronic ballasts:	Type-dependent
Cable length	
- Load:	Max. 100 m

- Control line:	Max. 100 m
Switch-on time:	10 seconds to 15 minutes
Ambient temperature:	+5 °C to +45 °C

Dimensions

Modular width (MW):	1
---------------------	---
