


Analogue actuator, 4-gang for KNX



| Specification | Order No. | Packing unit | £/piece without VAT | PS | EAN |
|--|-----------|--------------|------------------------|----|---------------|
|  DRA | 1022 00 | 1 | 378.58 | 26 | 4010337010708 |

Features

- Analogue actuator, 4-gang DRA with integrated bus coupler converts KNX telegrams (1-byte and 2-byte) into analogue output signals.
- These analogue output signals enable heating, air conditioning and ventilation actuators to adapt their initial parameters based on bus information, and to participate in control processes.
- Voltage outputs with short-circuit protection.
- The initial state is indicated by the status LED.
- The initial parameters can be restrained.
- Switch off outputs not required.
- The four outputs are parameterised to voltage or current signals by the software.

Technical data

| | |
|-------------------------------|----------------------------------|
| KNX medium: | TP256 |
| Number of outputs: | 4 |
| Rated voltage: | AC 24 V |
| Connections | |
| - KNX: | Connection and junction terminal |
| - Power supply: | Screw terminals |
| - Outputs: | Screw terminals |
| Current signals at the output | |
| - 0 to 20 mA: | Load \leq 500 Ω |
| - 4 to 20 mA: | Load \leq 500 Ω |
| Voltage signals at the output | |
| - 0 to 1 V: | Load \geq 1 k Ω |
| - 0 to 10 V: | Load \geq 1 k Ω |
| Connection cross section: | Max. 4 mm ² |
| Ambient temperature: | -5 °C to +45 °C |

Scope of supply

- Connection and junction terminal for KNX included with delivery.

Dimensions

Modular width (MW): 4
