


Flush-mounted DCS switching actuator



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
	1211 00	1/5	72.29	18	4010337211006

Features

- Flush-mounted switching actuator for controlling an external gong or other device using the Gira door communication bus.
- Actuation of a zero-voltage switching contact (24 V SELV/ 50 µA to 1.6 A AC/DC) via the 2-wire bus.
- The flush-mounted switching actuator can be actuated by: the "Door" and "Light" buttons on the home station, the floor-call button on the home station, the call button on the door station, the call button on the home station, a zero-voltage button (in combination with the DCS button interface, 2-gang).
- The flush-mounted switching actuator can be used in four different operating modes: switching, timer/sec., timer/min., and pulse.
- Impulse function for controlling existing automatic staircase mechanisms.
- Switching time can be adjusted progressively from 1 to 10 s or 1 to 10 min., depending on the function set.
- LED display for programming, function selection, and time setting.

Technical data

Power supply:	via the 2-wire bus
Zero-voltage relay contact:	50 µA to 1.6 A at AC/DC 24 V SELV
Number of call buttons that can be taught in:	max. 16
Ambient temperature:	-5 °C to +50 °C

Notes

- The flush-mounted switching actuator is intended for installation in a deep device box (60 mm deep) behind a DSC bus coupler.

Dimensions in mm

Flush-mounted switching actuator:	B 43	H 28	T 15
-----------------------------------	------	------	------