


## External camera



Specification	Order No.	Packing unit	PS	EAN
 pure white	1220 00	1	10	4010337100058

## Features

- External camera for wall or ceiling mounting with variable lens, integrated IR LED illumination, and automatic white balance.
- The camera can be installed anywhere in the entrance area and be integrated into the Gira door communication system using the DCS camera gateway.
- Light-sensitive chip set for clear imaging in low-light conditions.
- Switchable IR LEDs for video monitoring in complete darkness.
- Camera module and housing for easy, rapid installation.
- Camera module adjustable on three axes.

## Technical data

Rated voltage:	DC 12 V +10 %
Current consumption	
- DC 12 V:	max. 500 mA
Connections:	1 x video (HD TVI, BNC), 1 x video (FBAS, BNC), 1 x power supply (DC)
Camera	
- Image sensor:	1/2.9" CMOS progressive scan
- Type:	Variable, manual
- Lens:	2.8 to 12 mm
- Resolution:	480 TVL
- Horizontal angle of vision:	28° to 85°
Day/night switching:	Electromechanical IR cut filter
Electronic shutter control:	1/50 to 1/50 000 s
Camera control:	On-screen display (OSD), joystick on cable
Minimal lighting	
- Day:	0.05 lx
- IR mode:	0 lx
IR LED:	24 LED

IR range:	20 m
Ambient temperature:	-20 °C to +60 °C
Protection class:	IP66
Humidity:	max. 90%
Weight:	approx. 660 g

---

## Dimensions in mm

External camera:	Ø 126	H 100,3
------------------	-------	---------

---