


## Built-in speaker



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
	1258 00	1	121.13	18	4010337258001

## Features

- Built-in speaker for mounting in letterbox systems, voice compartments, door-side installations or front plates.
- Up to eight mechanical bell buttons can be connected to the screw terminals provided.
- Signal transmission and power supply of speaker via reverse-polarity-protected and short-circuit-proof 2-wire bus.
- Compact size.
- Weather-resistant speaker.
- High-quality electret microphone.
- Alternating current polling of the bell button connections to prevent oxidation on the button contacts.
- Securing of connection terminals against incorrect connection.
- Up to eight mechanical bell buttons can be connected.
- Colour camera for door station can be connected.
- Speakerphone function (voice-controlled talk-back with echo and background noise suppression).
- Adjustable voice volume.
- One-man start-up with easy start-up procedure.
- Audible acknowledgement signal when a call button is pressed.

## Technical data

Power supply: DC 26 V  $\pm$  2 V (via 2-wire bus)

### Connections

- 2-wire bus: 2x screw terminals
- Additional power supply: 2x screw terminals
- Mechanical bell button: 8 x screw terminal
- Common earth of bell buttons: 1 x screw terminal
- Connection cable: 2 x connector strip
- Video: 1 x connector strip

Protection type: IP44

Ambient temperature: -25 °C to +70 °C

## Notes

- This component enables door communication systems with up to 140 audio devices to be set up (e.g. 1 x built-in speaker, 11 x add-on modules for built-in speakers, 136 x surface-mounted home stations).
- The video control device is required if the system is extended with a colour camera.
- Protection type IP44 only in combination with a suitable front or when installed.

---

## Dimensions in mm

W 101      H 67      D 27

---