


Add-on module for built-in speaker



| Specification | Order No. | Packing unit | PS | EAN |
|---|-----------|--------------|----|---------------|
|  | 1259 00 | 1 | 18 | 4010337259008 |

Features

- Up to twelve mechanical bell buttons can be connected.
- Additional bell buttons can be connected via additional add-on modules.
- Up to eleven add-on modules can be connected to one built-in speaker.
- Alternating current polling of the bell button connections to prevent oxidation on the button contacts.
- Compact size.
- Securing of connection terminals against incorrect connection.
- Attachment of the add-on module with screws or gluing.

Technical data

| | |
|---------------------------------|---------------------|
| Connections | |
| - Mech. Bell button: | 12 x screw terminal |
| - Common earth of bell buttons: | 1 x screw terminal |
| - Connection cable: | 2 x connector strip |
| Protection class: | IP44 |
| Ambient temperature: | -25 °C to +70 °C |

Notes

- Module for extension of the built-in speaker when more than eight mechanical bell buttons are to be connected.
- This component enables door communication systems with up to 140 audio devices to be set up (e.g. 1 x built-in speaker, 11 x add-on modules for built-in speakers, 136 x surface-mounted home stations).
- Protection type IP44 only in combination with a suitable front or when installed.

Scope of supply

- The mounting materials are included in the scope of supply.

Dimensions in mm

| | | | |
|---------------------|------|--------|------|
| incl. fixing lug: | B 67 | H 66,4 | T 27 |
| without fixing lug: | B 67 | H 56 | T 27 |
