


Add-on module for built-in speaker



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
	1259 00	1	101.87	18	4010337259008

Features

- Up to twelve mechanical bell buttons can be connected.
- Additional bell buttons can be connected via additional add-on modules.
- Up to eleven add-on modules can be connected to one built-in speaker.
- Alternating current polling of the bell button connections to prevent oxidation on the button contacts.
- Compact size.
- Securing of connection terminals against incorrect connection.
- Attachment of the add-on module with screws or gluing.

Technical data

Connections	
- Mech. Bell button:	12 x screw terminal
- Common earth of bell buttons:	1 x screw terminal
- Connection cable:	2 x connector strip
Protection class:	IP44
Ambient temperature:	-25 °C to +70 °C

Notes

- Module for extension of the built-in speaker when more than eight mechanical bell buttons are to be connected.
- This component enables door communication systems with up to 140 audio devices to be set up (e.g. 1 x built-in speaker, 11 x add-on modules for built-in speakers, 136 x surface-mounted home stations).
- Protection type IP44 only in combination with a suitable front or when installed.

Scope of supply

- The mounting materials are included in the scope of supply.

Dimensions in mm

incl. fixing lug:	B 67	H 66,4	T 27
without fixing lug:	B 67	H 56	T 27
