



Surface-mounted door station video, 1 gang



| Specification | Order No. | Packing unit | £/piece without VAT | PS | EAN |
|--|-----------|--------------|------------------------|----|---------------|
|  pure white | 1269 66 | 1 | 1,025.64 | 10 | 4010337269663 |
|  anthracite | 1269 67 | 1 | 1,036.85 | 10 | 4010337269670 |
|  colour aluminium | 1269 65 | 1 | 1,036.85 | 10 | 4010337269656 |

Features

- Fully pre-assembled surface-mounted door station for vertical surface-mounted installation. This facilitates fast and clean installation.
- In the design of the Gira TX_44 design line.
- Torsion-resistant surface-mounted housing due to aluminium profile.
- Frame made of shatter-proof thermoplastic with high resistance to ultraviolet light as well as a scratch-resistant, care-free surface.
- Theft protection ensured by screws with hexalobular socket.
- Signal transmission and supply of the audio and video components via reverse-polarity-protected and short-circuit-proof 2-wire bus.
- One-man commissioning with simple commissioning procedure.
- Weather-resistant loudspeaker.
- High-quality electret microphone.
- Hands-free feature (voice-controlled talk-back with echo and background noise suppression).
- Acknowledgement tone when call button is pressed.
- Voice volume adjustable.
- White call-button illumination with LED technology. Even, clearly visible call button illumination is achieved via maintenance-free, energy-saving LED technology.
- Sprayed-water proof call-button cover plate made of shock-resistant plastic.
- Name plate of the call button can be exchanged without tools and frame removal.
- Professional inscription by the Gira inscription service www.beschriftung.gira.de or the Gira inscription software.
- Door station with colour camera, door loudspeaker, and call button.
- Automatic day or night switching: the camera switches from day mode (colour display) to night mode (black and white display) and back again at a defined ambient brightness. Due to the high degree of light sensitivity in night mode, good presentation results are achieved even in poor lighting conditions.
- LEDs ensure steady illumination of the field of view at close proximity in night mode.

- Camera can be manually pivoted 20° horizontally and vertically. In combination with the wide-angle lens, a very wide field of view results.
- Automatic background lighting compensation.
- Automatic white balance.
- Automatic gain control (AGC).
- Integrated camera heating with temperature detection.
- Sprayed-water proof cover plate.
- Camera cover plate made of impact-resistant plastic. Easy to replace if damaged, e.g. due to vandalism.

Technical data

| | |
|---|-------------------------------|
| Power supply: | DC 26 V ± 2 V (by 2-wire bus) |
| Connections | |
| - 2-wire bus: | 2 x screw terminal |
| - Additional power supply: | 2 x screw terminal |
| Protection class: | IP44 |
| Ambient temperature: | -25 °C to +70 °C |
| Image capture element: | CCD sensor 0.85 cm (1/3") |
| Wide-angle lens: | 150° |
| Visible range of detection: | 100° |
| Detection range (when pivoted by 20°): | 140° |
| Colour system: | PAL |
| Pixels: | 500 (H) x 582 (V) |
| Horizontal resolution: | 380 TV lines |
| Switchover threshold for colour to B/W operation: | 1 lx |
| Light sensitivity in B/W operation: | 0.1 lx |
| Electronic shutter speed: | up to 1/100000 s |
| IR filter: | integrated |
| Recommended installation height for camera: | 1.50 m |

Dimensions in mm

| | | | |
|-----------------|-------|-------|------|
| without camera: | B 110 | H 253 | T 19 |
| with camera: | B 110 | H 253 | T 40 |
| Name plate: | B 62 | H 62 | T - |