



## Light profile height 491 mm



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 anthracite	1344 28	1	477.30	17	4010337344285
 colour aluminium	1344 26	1	518.27	17	4010337344261

Gira energy profile and light profiles with or without light elements for outdoor use. The profiles are made of powder-coated aluminium. For profiles of up to 1400 mm, the base elements are also made of powder-coated aluminium. For profiles of 1400 mm or more, the base elements are made of powder-coated steel. In each case, in the colour anthracite in accordance with the GSB standard. The surface is resistant to weather, UV, soiling, and scratching.

### Features

- The light element consists of an aluminium reflector and an impact-resistant acrylic glass plate.
- Light is also emitted from the rear as orientation light.
- The connection is made using a 5-pole screw terminal for rigid and flexible conductors up to 4 mm<sup>2</sup>.

### Technical data

Protection type: IP44

### Notes

- For profile heights up to 1400 mm, an optional ground anchor can be used to facilitate mounting on a stone or concrete base.
- For profile heights of more than 1400 mm, mounting on stone or concrete is only possible using 3 heavy-duty wall anchor.
- Recommendation: Mount an RCCB prior to the device.
- Single-wall plug mounting.
- Light sources with E27 treading of the energy efficiency classes A++ to E can be used.

## Scope of supply

- The mounting materials are included in the scope of supply.
  - Light sources are not included in the scope of supply.
- 

## Dimensions in mm

Base:	W 229	H 10	D 155
Profile:	W 142	H 491	D 75

---