



## Gira energy profile with light element and 3 empty units height 1600 mm not equipped



| Specification  | Order No. | Packing unit | PS | EAN           |
|--|-----------|--------------|----|---------------|
|  anthracite        | 1353 28   | 1            | 17 | 4010337353287 |
|  colour aluminium | 1353 26   | 1            | 17 | 4010337353263 |

Gira energy profile and light profiles with or without light elements for outdoor use. The profiles are made of powder-coated aluminium. For profiles of up to 1400 mm, the base elements are also made of powder-coated aluminium. For profiles of 1400 mm or more, the base elements are made of powder-coated steel. In each case, in the colour anthracite in accordance with the GSB standard. The surface is resistant to weather, UV, soiling, and scratching.

### Features

- Freely configurable Gira energy profile with 3 empty units and light element.
- The light element consists of an aluminium reflector and an impact-resistant acrylic glass plate.
- Light is also emitted from the rear as orientation light.
- The three empty units can be individually equipped with device inserts from the TX\_44 design line or from System 55 by the customer.

### Technical data

Protection type (device cover closed): IP44

### Notes

- For profile heights up to 1400 mm, an optional ground anchor can be used to facilitate mounting on a stone or concrete base.
- For profile heights of more than 1400 mm, mounting on stone or concrete is only possible using 3 heavy-duty wall anchor.
- Recommendation: Mount an RCCB prior to the device.
- Mounting using three heavy-duty wall anchors.
- Suitable for E27 light sources with energy efficiency classes A++ to E.
- Any required electrical isolation of mains and low voltage can be implemented with the included accessories.

## Scope of supply

- Cover frame, 3-gang TX\_44 is included in the scope of supply.
- The mounting materials are included in the scope of supply.
- Light sources are not included in the scope of supply.

---

## Dimensions in mm

|          |       |        |       |
|----------|-------|--------|-------|
| Base:    | B 229 | H 10   | T 155 |
| Profile: | B 142 | H 1600 | T 75  |

---