



## Pushbutton sensor 2, 1-gang 24 V zero-voltage with inscription space



| Specification   | Order No. | Packing unit | PS | EAN           |
|---|-----------|--------------|----|---------------|
|  clear / pure white glossy | 2001 100  | 1            | 02 | 4010337047988 |
|  stainless steel         | 2001 600  | 1            | 02 | 4010337020356 |

### Features

Pushbutton sensor 2 for connection to 24 V control systems

- Rocker with two red LEDs for status display.
- Safeguarded from disassembly because it is screw-fastened.
- Backlighting.
- Connection of two buttons, two LEDs and backlighting using terminal block on the rear.

### Technical data

|                                    |                            |
|------------------------------------|----------------------------|
| Rated voltage of each push button: | AC/DC 24 V SELV            |
| Load capacity of each push button: | max. 20 mA                 |
| Rated voltage of each LED:         | DC 24 V SELV               |
| Load capacity of each LED:         | 1 mA                       |
| Connection:                        | 2 x terminal block, 9-pole |
| Connection cross section:          | 0.4 to 0.8 mm single-wire  |
| Installation depth:                | 25 mm                      |
| Ambient temperature:               | -5 °C to +45 °C            |

## Notes

- Suitable for SELV circuits only.
  - Can also be connected to be illuminated.
  - Professional inscription by the Gira inscription service [www.marking.gira.com](http://www.marking.gira.com).
- 

## Scope of supply

- Plain inscription labels included.
-