



## Pushbutton sensor 2, 3-gang 24 V zero-voltage with inscription space



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 clear / pure white glossy	2003 100	1	87.79	02	4010337047971
 stainless steel	2003 600	1	101.64	02	4010337020363

### Features

Pushbutton sensor 2 for connection to 24 V control systems

- Three rockers with two red LEDs for status display each.
- Safeguarded from disassembly because it is screw-fastened.
- Backlighting.
- Connection of six buttons, six LEDs, and backlighting using terminal block on the rear.

### Technical data

Rated voltage of each push button:	AC/DC 24 V SELV
Load capacity of each push button:	max. 20 mA
Rated voltage of each LED:	DC 24 V SELV
Load capacity of each LED:	1 mA
Connection:	2 x terminal block, 9-pole
Connection cross section:	0.4 to 0.8 mm single-wire
Installation depth:	25 mm
Ambient temperature:	-5 °C to +45 °C

## Notes

- Suitable for SELV circuits only.
  - Can also be connected to be illuminated.
  - Professional inscription by the Gira inscription service [www.marking.gira.com](http://www.marking.gira.com).
- 

## Scope of supply

- Plain inscription labels included.
-