


Blind actuator, 2-gang AC 230 V with manual actuation for KNX



| Specification | Order No. | Packing unit | £/piece without VAT | PS | EAN |
|--|-----------|--------------|------------------------|----|---------------|
|  DRA | 2152 00 | 1 | 160.20 | 26 | 4010337082231 |

Blind actuators with integrated bus coupler, manual activation, and status display for each output. For controlling electrically operated blinds, shutters, awnings, ventilation flaps, or similar hangings.

Features

- Curtain position can be directly controlled.
- Slat position can be directly controlled.
- Behaviour after bus voltage failure and recovery can be set.
- Separately parameterizable movement times with movement time extension for moving into the upper end position.
- Central control of all blind outputs possible.
- Feedback on the curtain or slat position.
- Feedback can be delayed until after the recovery of bus voltage.
- Assignments of up to five different safety functions (three wind alarms, one rain alarm, one frost alarm) or optionally with cyclical monitoring.
- Forced setting function can be realised for each blind output.
- Integration in scenes is possible, 8 internal scenes at the most can be parameterised per channel.
- Memory function for light scenes.
- Solar protection function with fixed and variable curtain or slat positions can be activated.
- Extended sun protection with extensive control functions.
- Integration in temperature management of building possible.
- Blocking of individual outputs manually or with bus.
- Active or passive (object can be read out) cyclical feedback functions.
- Building site operation: Outputs can be operated manually without bus voltage with operating voltage only.
- For mains voltage AC 230 V.
- Connection of various external conductors.
- Independent control of the two blind outputs.
- Automatic detection of hanging travel time for AC 230 V drives with mechanical limit switches.

Technical data

| | |
|-------------|----------------------------------|
| KNX medium: | TP256 |
| Connections | |
| - KNX: | Connection and junction terminal |

| | |
|-----------------------------|------------------------|
| - Load: | Screw terminals |
| Rated voltage: | AC 230 V, 50/60 Hz |
| AC switching voltage: | AC 230 V, 50/60 Hz |
| Breaking capacity 230 V AC: | 6 A/AC1 |
| Switching voltage DC: | DC 12 to 48 V |
| Switching capacity | |
| - DC 12/24 V: | 6 A |
| - DC 48 V: | 3 A |
| Connection cross section: | Max. 4 mm ² |

Notes

- Installation on DIN top-hat rail.
-

Scope of supply

- Connection and junction terminal for KNX included in the scope of supply.
-

Dimensions

| | |
|---------------------|---|
| Modular width (MW): | 4 |
|---------------------|---|
