

Shutter actuator, 4-gang AC 230 V with manual actuation for KNX



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 DRA	2160 00	1	236.69	26	4010337101352

Features

- Shutter actuator with manual activation and status display for each output.
- With integrated bus coupler.
- For controlling electrically operated shutters for mains voltage AC 230 V (4-channel).
- Connection of various external conductors.
- Independent control of the four shutter outputs.
- Shutter position can be directly controlled.
- Behaviour after bus voltage failure and recovery can be set.
- Feedback of position. Active or passive (object can be read out) cyclical feedback functions.
- Assignments of up to five different safety functions (three wind alarms, one rain alarm, one frost alarm) or optionally with cyclical monitoring.
- Building site operation: Outputs can be operated manually without bus voltage with operating voltage only.

Technical data

KNX medium:	TP256
Rated voltage:	AC 230 V, 50/60 Hz
AC switching voltage:	AC 230 V, 50/60 Hz
Breaking capacity 230 V AC:	6 A/AC1
Connections	
- KNX:	Connection and junction terminal
- Load:	Load via screw terminals
Connection cross section:	Max. 4 mm ²

Notes

- VDE approval in accordance with EN 60669-1, EN 60669-2-1.
 - Installation on DIN top-hat rail.
-

Scope of supply

- Connection and junction terminal for KNX included with delivery.
-

Dimensions

Modular width (MW): 4
