


Fan coil actuator for KNX



| Specification | Order No. | Packing unit | £/piece without VAT | PS | EAN |
|--|-----------|--------------|------------------------|----|---------------|
|  DRA | 2163 00 | 1 | 313.69 | 26 | 4010337059387 |

Features

- Fan coil actuator for operation of ventilator convectors (fan coil units), implemented for room air conditioning.
- The actuator receives telegrams, e.g. from a room temperature controller, and converts variable telegrams into equivalent fan speeds and valve positions.
- Connection of a ventilator convector with up to six ventilator gradations or connection of two ventilator convectors each with up to three fan speeds with double pipe systems.
- Manual actuation.
- Building site operation: Outputs can be operated manually without bus voltage with operating voltage only.
- Operating modes for heating or cooling, or combined heating and cooling.
- 2-pipe or 4-pipe operation. 2-pipe system uses a shared water circuit for heating and cooling. 4-pipe system consists of separate supply and return line for the heating and cooling system.
- Individual or hierarchic switching of fan speeds.
- Feedback, output indication, block function for each channel, level limitation.
- Behaviour after bus voltage failure or bus/mains voltage failure and following an ETS programming process can be configured.
- Limit values can be set.
- Cyclical or event-oriented transmission.
- Free channels can be used for switching functions, e.g. for room lighting.

Technical data

| | |
|-----------------------------|--|
| KNX medium: | TP256 |
| Switching contact: | μ contact, 1 x zero-voltage NO contact |
| Breaking capacity 230 V AC: | 10 A / AC1 or 10 A / AC3 |
| Maximum switch-on current | |
| - 200 μs: | 800 A |
| - 20 ms: | 165 A |
| Connected load | |
| - Ohmic load: | 2300 W |
| - Capacitive load 230 V AC: | 10 A, max. 140 μF |
| - Light bulbs: | 2300 W |
| - HV halogen lamps: | 2300 W |

| | |
|---|---------|
| - Wound electronic transformer: | 1200 VA |
| - Tronic transformer: | 1500 W |
| - Fluorescent lamps, uncompensated: | 1000 VA |
| - Fluorescent lamps, lead-lag circuit: | 2300 VA |
| - Fluorescent lamps, parallel-compensated: | 1160 VA |
| - Mercury-vapour lamps, uncompensated: | 1000 W |
| - Mercury-vapour lamps, parallel-compensated: | 1160 W |

Connections

| | |
|---------|----------------------------------|
| - KNX: | Connection and junction terminal |
| - Load: | Screw terminals |

| | |
|---------------------------|------------------------|
| Connection cross section: | Max. 4 mm ² |
|---------------------------|------------------------|

Notes

- VDE approval in accordance with EN 60669-1, EN 60669-2-1.
 - Installation on DIN top-hat rail.
-

Scope of supply

- Connection and junction terminal for KNX included in the scope of supply.
-

Dimensions

| | |
|---------------------|---|
| Modular width (MW): | 4 |
|---------------------|---|
