


## System 3000 universal LED power booster DRA



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 DRA	2383 00	1	130.12	02	4010337031383

### Features

- Switching and dimming light bulbs, HV halogen lamps, electronic transformers for halogen, inductive transformers for halogen, HV LED or compact fluorescent lamps.
- Operation is via upstream dimmer.
- The connected loads are supplied via a common load line.
- Electronic excess-temperature protection.

### Technical data

Rated voltage:	AC 230 V, 50/60 Hz
Standby:	0.3 W
Connected load at 45 °C	
- HV LED lamps (leading edge):	50 to 100 W
- HV LED lamps (trailing edge):	200 W
- Light bulbs:	210 to 420 W
- HV halogen lamps:	210 to 420 W
- Tronic transformers:	210 to 420 W
- Wound electronic transformer:	210 to 420 VA
Cable length	
- Load:	Max. 100 m
Ambient temperature:	-5 °C to +45 °C

### Notes

- If the ambient temperature is higher than 45 °C, the connected load must be reduced.
- Maximum load and number of power boosters depend on dimmer. Refer to the technical appendix or operating instructions for a reference list.

## Dimensions

Modular width (MW): 2

---