


UPS for emergency set



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 pure white glossy	2918 03	1/5	223.43	34	4010337011767

Features

- Uninterruptible power supply for the Gira emergency set.
- If the mains input voltage drops or fails, the connected load continues to be supplied by the rechargeable battery without interruption.
- If the mains input voltage increases or is restored, the rechargeable battery is disconnected from the load and recharged in normal mains operation.
- The signal contact (M) can be used to signal the operating statuses "UPS active" or "Rechargeable battery defective".

Technical data

Input voltage:	DC 24 V
Output voltage in rechargeable battery operation:	22.8 V \pm 10%
Rated load in rechargeable battery operation:	130 mA for 1 h
Maximum load - in rechargeable battery operation:	300 mA for 15 min
Battery/rechargeable battery - Type:	UR18500F
- UN no.:	3480
Maximum load - in mains operation:	250 mA
Installation:	in device box in accordance with DIN 49073

Notes

- For installations in accordance with DIN VDE 0834.
 - DIN VDE 0834 states that components with a limited service life (rechargeable battery) must be replaced 1 x per year.
 - Please observe the regulations on the disposal of used batteries.
-

Scope of supply

- Blank cover plate is included in the scope of supply.
 - Battery included in the scope of supply.
-