









**Socket outlet with earth pin 16 A 250 V~  
and increased contact protection (Safety Plus)  
System 55**



| Specification   | Order No. | Packing unit | £/piece<br>without VAT | PS | EAN           |
|---|-----------|--------------|------------------------|----|---------------|
|  cream white glossy | 4485 01   | 1/5          | 10.86                  | 01 | 4010337095668 |
|  pure white glossy | 4485 03   | 10/100       | 10.86                  | 01 | 4010337095682 |
|  pure white matt   | 4485 27   | 10           | 10.86                  | 01 | 4010337095712 |
|  anthracite        | 4485 28   | 10           | 11.97                  | 11 | 4010337095729 |
|  colour aluminium  | 4485 26   | 10           | 15.89                  | 11 | 4010337095705 |
|  black matt        | 4485 005  | 10           | 15.89                  | 11 | 4010337095651 |
|  grey matt         | 4485 015  | 1/5          | 15.89                  | 11 | 4010337095675 |
|  stainless steel   | 4485 600  | 1/5          | 22.93                  | 11 | 4010337095736 |

## Features

- With plug terminals.
  - The support ring is earthed in connection with the mounting claws and claw screws.
  - Quick mounting (approx. 3.5 turns per mounting claw).
  - Expanding claws in the housing.
  - Easier claw mounting thanks to robust PZ1 / slotted / PH screw head drive.
  - Simplified installation thanks to patented arrangement of the large keyhole profiles using box screws.
  - Low installation depth.
  - Large, ergonomically shaped release levers.
  - Sturdy earth bar with solid earthing fingers.
  - Sturdy and corrosion-resistant steel support ring.
  - Shatter-proof thermoplastic base.
- 

## Technical data

|                                     |  |
|-------------------------------------|--|
| Installation depth:                 | 29 mm                                      |
| Replaces fully compatible 0485 ...: |  |
| Connection cross section            |  |
| - for conductors from:              | 1.5 mm <sup>2</sup> to 2.5 mm <sup>2</sup> |
| Ambient temperature                 |  |
| - increased contact protection:     | 0°C to +45°C                               |

---

## Notes

- Approved in accordance with NBN C 61-112-1:2017.
  - Increased contact protection (Safety Plus) in accordance with IEC 60884-1.
-