



Pushbutton sensor 4 24 V, 1-gang



Specification	Order No.	Packing unit	£/piece without VAT	PS	EAN
 white	5051 003	1	66.69	02	4010337074960
 anthracite	5051 028	1	66.69	02	4010337074977

Features

- Pushbutton sensor 4 for connection to 24 V control systems.
- Operating surface made of high-quality three-millimetre thick real material (glass, stainless steel, aluminium).
- Two white status LEDs per rocker.
- Measurement of the room temperature with integrated temperature sensor (PT1000).

Technical data

Button

- Rated voltage: AC/DC 24 V SELV
- Current capacity: 20 mA per button
- Output resistance: 880 Ω

LED

- Rated voltage: DC 24 V SELV
- Current consumption: approx. 1 mA per LED

Temperature sensor: PT1000, class B

Protection class: III

Installation depth: 16 mm

Ambient temperature: -5 °C to +45 °C

Notes

- Suitable for SELV circuits only.
 - Professional labelling with the Gira Inscription Service www.marking.gira.com.
 - The pushbutton sensor is supplied with a program-neutral start-up rocker. The suitable rocker set for the design line must be ordered separately.
-